

Application Note – 3 Set Speeds of Operation

DART CONTROLS DC motor speed controls can be configured for field selectable 3 set speeds of operation by connecting a switch in the potentiometer circuit. The 3 set speeds are as follows:

- 1) High Speed – Maximum speed set by the board mounted max speed pot
- 2) Mid Speed – Adjustable speed set by the main speed pot
- 3) Low Speed – Minimum speed set by the board mounted min speed pot

Valid For Models:

Any DART CONTROLS motor control with an adjustable speed potentiometer.

SCR Series: **500, 250, 130, 125**

PWM Series: **DPW**

Battery Operated Series: **65**

Brushless Series: **700**

DART CONTROLS offers both AC and DC motors and controls. Feel free to contact us for assistance in selecting the right AC or DC motor and control for your application.

